

Rittal – The System.

Faster – better – everywhere.



AS 4050.887

Circular thread milling cutter

State: 2025-07-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.887 - Circular thread milling cutter

Milling cutter for cutting metric threads for the Perforex machining center BC and Perforex Milling Terminal MT.

Features

Model No.	AS 4050.887
Product description	Milling cutter for cutting metric threads for the Perforex machining center BC and Perforex Milling Terminal MT.
Technical specifications	Shaft diameter 12 mm Cutting diameter 10 mm Pitch 1.5 mm Flank angle 60° Cutting length 20 mm Total length 85 mm
For thread	M16 - M64
Standards	DIN 13-1 metric ISO thread
Workable material	Steel Stainless steel Cast aluminum Plastic Copper
Packaging unit	1 pc(s).
Net weight	0.05
Gross weight	0.05
Customs tariff number	82077031
EAN	4028177805286
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609211