
# Rittal – The System.

Faster - better - everywhere.





# AS 4050.737 Wire end ferrule

State: 2025-11-12 (Source: rittal.com/ca-en)



## AS 4050.737 - Wire end ferrule Loose

With plastic collar.

#### **Features**

Model No.	AS 4050.737
Version	For manual assembly for fully automated wire cabling machine Wire Terminal WT C
Product description	With plastic collar.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	White
Length	12 mm
AWG	20
Internal diameter	2.6 mm
For cross section	0.5 mm²
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines. For tailored advice, please contact a Rittal representative.
Standards	AEH DIN 46228
Suitable for Model No.	4051.205 4051.210
Delivery form	Loose (10 packs of 100)
Packaging unit	1,000 pc(s).
Net weight	1
Gross weight	0.105
Customs tariff number	85369010

© Rittal 2025

### Features

EAN	4028177805057
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3