

Rittal – The System.

Faster – better – everywhere.



AS 4051.100

Wire Station WS 540

State: 2026-01-23 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.100 - Wire Station WS 540

Mobile wiring workstation, height-adjustable and flexible use in the workshop. Allows ergonomic and fatigue-free work across wire processing tasks.



Features

Model No.	AS 4051.100
Version	Standard
Product description	Mobile wiring workstation, height-adjustable and flexible use in the workshop. Allows ergonomic and fatigue-free work across wire processing tasks.
Benefits	<p>Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm</p> <p>Multiplex worktop, washable and scratch-resistant</p> <p>Ideal solution when combined with the cutting and crimping machines as well as the use of pre-assembled wires through the wire terminal</p> <p>Integrated scale for quick manual measurements</p> <p>Prepared to accommodate a monitor for wire processing with Eplan Smart Wiring</p> <p>Optionally expandable with shelves for wire cartons, wire rolls and holders for tools and small parts</p> <p>Versatile use in workshop due to rubberized rollers</p> <p>Drawer with shadowboard prepared for tools</p>
Supply includes	<p>Wiring table with electrical height adjuster</p> <p>Connection cable, 7 m</p> <p>Socket strip, 7-way, with rocker switch</p>
Mounting tip	The mounting stay, vertical, Order No. 4051.106, is required for accessories such as storage box holders, magazine supports, etc.

Features

Input voltage	230 V AC, 50 Hz
Dimensions	Width: 900 mm Height: 1,350 mm Depth: 781 mm
Working height	Working height (min.): 710 mm Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Packaging unit	1 pc(s).
Net weight	95
Gross weight	107
Customs tariff number	94032080
EAN	4028177957480
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	21100204

Approvals

Explanations	Declaration of conformity
--------------	---------------------------
