Rittal – The System.

Faster – better – everywhere.





AS 4051.100 Wire Station WS 540

State: 2025-10-22 (Source: rittal.com/ca-en)



AS 4051.100 - Wire Station WS 540

Mobile wiring workstation, height-adjustable and flexible use in the workshop. Allows ergonomic and fatigue-free work across wire processing tasks.







Features

Model No.	AS 4051.100
Version	Standard
Product description	Mobile wiring workstation, height-adjustable and flexible use in the workshop. Allows ergonomic and fatigue-free work across wire processing tasks.
Benefits	Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm
	Multiplex worktop, washable and scratch-resistant
	Ideal solution when combined with the cutting and crimping
	machines as well as the use of pre-assembled wires through the wire terminal
	Integrated scale for quick manual measurements
	Prepared to accommodate a monitor for wire processing with Eplar Smart Wiring
	Optionally expandable with shelves for wire cartons, wire rolls and holders for tools and small parts
	Versatile use in workshop due to rubberized rollers
	Drawer with shadowboard prepared for tools
Supply includes	Wiring table with electrical height adjuster
	Connection cable, 7 m
	Socket strip, 7-way, with rocker switch
Mounting tip	The mounting stay, vertical, Order No. 4051.106, is required for accessories such as storage box holders, magazine supports, etc.

© Rittal 2025

Features

Input voltage	230 V AC, 50 Hz
Dimensions	Width: 900 mm Height: 1,350 mm Depth: 781 mm
Working height	Working height (min.): 710 mm Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Packaging unit	1 pc(s).
Net weight	95
Gross weight	107
Customs tariff number	94032080
EAN	4028177957480
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	21100204

Approvals

|--|

© Rittal 2025 3