

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.601 Wire end ferrule

State: 2026-03-05 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.601 - Wire end ferrule on belt

With plastic flange.

## Features

Model No.	AS 4051.601
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Yellow
Length	8 mm
AWG	18
Internal diameter	3 mm
Rittal color code	Yes
For cross section	1 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5 kg
Gross weight	0.645 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Features

---

Product description

Wire end ferrules for crimping machines, 1 mm<sup>2</sup>, AWG 18, 8 mm, yellow, on belt, 5000 pc(s).

# Approvals

---

Approvals

UL + C-UL (listed)  
UR