Rittal – The System.

Faster - better - everywhere.





AS 4052.102 Screwdriver

State: 2025-10-24 (Source: rittal.com/ca-en)



AS 4052.102 - Screwdriver Insulated

With a long, slender handle and high-performance tip with insulation.



Features

Model No.	AS 4052.102
Version	With 1000 V protective insulation For slotted screws
Product description	With a long, slender handle and high-performance tip with insulation.
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with roll-off protection and clear screw marking Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than that of a comparable tool Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working
Material	Blade: Chromium molybdenum vanadium alloy Inside of handle: Hard plastic Handle body: elastic, highly flexible plastic
Color	Handle: Anthracite and Rittal Power Pink
Blade dia.	3.5 mm
Blade length	100 mm
Blade (width x thickness)	3.5 x 0.6 mm
Output	SL
Handle dia.	25 mm
Handle length	105 mm

© Rittal 2025

Features

Standards	IEC 60 900
Packaging unit	3 pc(s).
Customs tariff number	82054000
EAN	4028177807211
ETIM 9	EC000144
ETIM 8	EC000158
ECLASS 8.0	21040406

© Rittal 2025 3