Rittal – The System.

Faster – better – everywhere.



AS 4054.003 Crimping tool

State: 2025-11-15 (Source: rittal.com/ca-en)



AS 4054.003 - Crimping tool For wire end ferrules

Crimping pliers for square or hexagonal compression for crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.

Features

Model No.	AS 4054.003	
Version	Straight	
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.	
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Unlockable forced lock Self-adjusting	
Material	High-grade special tool steel	
Surface finish	Matt, chromium-plated	
Color	Handle: Anthracite and Rittal Power Pink	
Crimping	Hexagonal crimp	
Cable entry direction	Side	
Dimensions	Length: 176 mm	
AWG	26 - 8	
For cross section	0.14 - 10 mm²	
Packaging unit	1 pc(s).	
Net weight	0.4	
Gross weight	0.455	
Customs tariff number	82032000	
EAN	4028177930964	
ETIM 9	EC000168	

© Rittal 2025 2

Features

ETIM 8	EC000168	
ECLASS 8.0	21043811	

© Rittal 2025 3