Rittal – The System.

Faster – better – everywhere.





AS 4052.142 Screwdriver

State: 2025-11-16 (Source: rittal.com/ca-en)



AS 4052.142 - Screwdriver Insulated

With a long, slender handle and high-performance tip with insulation.

Features

Model No.	AS 4052.142	
Version	With 1000 V protective insulation For positive/negative	
Product description	With a long, slender handle and high-performance tip with insulation.	
Benefits	Minimal force required, thanks to ergonomically styled handle Handle head with roll-off protection and clear screw marking Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than that of a comparable tool Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working	
Material	Blade: Chromium molybdenum vanadium alloy Inside of handle: Hard plastic Handle body: elastic, highly flexible plastic	
Color	Handle: Anthracite and Rittal Power Pink	
Blade dia.	6 mm	
Blade length	100 mm	
Output	Gear wheel 2	
Handle dia.	27 mm	
Handle length	115 mm	
Standards	IEC 60 900	
Packaging unit	3 pc(s).	
Customs tariff number	82054000	
EAN	4028177807303	
ETIM 9	EC000144	

© Rittal 2025

Features

ETIM 8	EC000144	
ECLASS 8.0	21040406	

© Rittal 2025 3