Rittal – The System.

Faster – better – everywhere.





AS 4054.004 Crimping pliers

State: 2025-11-17 (Source: rittal.com/ca-en)



AS 4054.004 - Crimping pliers For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



Features

Model No.	AS 4054.004
Version	Straight
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Labeled die stations for precise machining of the relevant cross sections Unlockable forced lock
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	WM crimp
Cable entry direction	Side
Dimensions	Height: 68 mm Length: 256 mm
AWG	8 - 4
For cross section	10 - 25 mm²
Packaging unit	1 pc(s).

© Rittal 2025

Features

Net weight	0.66
Gross weight	0.69
Customs tariff number	82032000
EAN	4028177807600
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811

© Rittal 2025 3