

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.000 Crimping pliers

State: 2025-08-23 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4054.000 - Crimping pliers For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



## Features

Model No.	AS 4054.000
Version	Angled
Product description	For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.
Benefits	Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Labeled die stations for precise machining of the relevant cross sections Unlockable forced lock
Material	High-grade special tool steel
Surface finish	Matt, chromium-plated
Color	Handle: Anthracite and Rittal Power Pink
Crimping	Trapezoid crimp
Cable entry direction	Side
Dimensions	Height: 59 mm Length: 198 mm
AWG	24 - 10
For cross section	0.25 - 6 mm <sup>2</sup>

# Features

Packaging unit	1 pc(s).
Net weight	0.439
Gross weight	0.449
Customs tariff number	82032000
EAN	4028177807587
ETIM 9	EC000168
ETIM 8	EC000168
ECLASS 8.0	21043811