Rittal – The System.

Faster - better - everywhere.





AS 4054.000 Crimping pliers

State: 2025-11-19 (Source: rittal.com/ca-en)



AS 4054.000 - Crimping pliers For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



Features

| Model No. | AS 4054.000 |
|-----------------------|--|
| Version | Angled |
| Product description | For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4. |
| Benefits | Minimal force required for large conductor cross-sections Pressing operation with a consistently high quality Labeled die stations for precise machining of the relevant cross sections Unlockable forced lock |
| Material | High-grade special tool steel |
| Surface finish | Matt, chromium-plated |
| Color | Handle: Anthracite and Rittal Power Pink |
| Crimping | Trapezoid crimp |
| Cable entry direction | Side |
| Dimensions | Height: 59 mm Length: 198 mm |
| AWG | 24 - 10 |
| For cross section | 0.25 - 6 mm² |

© Rittal 2025

Features

| Packaging unit | 1 pc(s). |
|-----------------------|---------------|
| Net weight | 0.439 |
| Gross weight | 0.449 |
| Customs tariff number | 82032000 |
| EAN | 4028177807587 |
| ETIM 9 | EC000168 |
| ETIM 8 | EC000168 |
| ECLASS 8.0 | 21043811 |

© Rittal 2025 3