

# Rittal – The System.

Faster – better – everywhere.



## AS 4054.030

### Flex crimping tool

State: 2026-01-14 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# AS 4054.030 - Flex crimping tool For wire end ferrules

For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | AS 4054.030   |
| Version               | Straight  |
| Product description   | For crimping wire end ferrules without an insulating sleeve according to DIN 46228 Part 1 and wire end ferrules with an insulating sleeve according to DIN 46228 Part 4.  |
| Benefits              | Front or side mounting of the wire end ferrule through a rotatable head<br>Minimal force required for large conductor cross-sections<br>Pressing operation with a consistently high quality<br>Unlockable forced lock<br>Self-adjusting |
| Material              | High-grade special tool steel   |
| Surface finish        | Coated, black, matt   |
| Color                 | Handle: Anthracite and Rittal Power Pink  |
| Crimping              | Trapezoid crimp   |
| Cable entry direction | front and side  |
| Dimensions            | Length: 180 mm  |
| AWG                   | 26 - 8  |
| For cross section     | 0.14 - 10 mm <sup>2</sup>   |
| Packaging unit        | 1 pc(s).  |

# Features

|                       |               |
|-----------------------|---------------|
| Net weight            | 0.35          |
| Gross weight          | 0.388         |
| Customs tariff number | 82032000      |
| EAN                   | 4028177955936 |
| ETIM 9                | EC000168      |
| ETIM 8                | EC000168      |
| ECLASS 8.0            | 21043811      |