

Rittal – The System.

Faster – better – everywhere.



AS 4054.870

Cross member cutter

State: 2026-02-10 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.870 - Cross member cutter

For cutting through micro ridges or cross members made of carbon steel on Ri4Power interior components (e.g. functional room dividers) or for cutting thin sheets of carbon steel, aluminum or copper up to a material thickness of 1.2 mm.



Features

Model No.	AS 4054.870
Version	Straight
Product description	For cutting through micro ridges or cross members made of carbon steel on Ri4Power interior components (e.g. functional room dividers) or for cutting thin sheets of carbon steel, aluminum or copper up to a material thickness of 1.2 mm.
Benefits	Cutting the materials without deformation Clean edge cuts, no reworking of the cut section required Easy to use Ergonomically shaped handles for fatigue-free and anti-slip work
Material	Tool body: Special tool steel, rolled, oil-hardened
Color	Handle: Anthracite and Rittal Power Pink
Supply includes	Cross member cutter, including splinter deflector

Features

Suitable for Model No.	9683.006 9683.008 9683.016 9683.018 9683.036 9683.038 9680.005 9680.025 9680.207 9680.227 9683.406 9683.408 9683.426 9683.428 9683.444 9683.446 9683.448 9683.464 9683.466 9683.468 9683.484 9683.486 9683.488
Dimensions	Length: 280 mm
Workable material	Carbon steel Aluminum Copper Plastic
Max. material thickness that can be machined for sheet steel	1.2 mm
Max. machinable material thickness, aluminum	1.2 mm
Max. machinable material thickness, plastic	2 mm
Cutting width	2.7 mm
Packaging unit	1 pc(s).
Net weight	0.5

Features

Gross weight	0.54
Customs tariff number	82032000
EAN	4028177955929
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
