

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.070**

**Manual hydraulic punch set, M16 -  
M63**

State: 2026-05-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.070 - Manual hydraulic punch set, M16 - M63

Manual hydraulic punch set with hole punches for carbon steel. Maximum machinable material thickness 2 or 3 mm.

## Features

Model No.	AS 4055.070
Version	This set includes the standard carbon steel punchers M16 to M63.
Product description	Manual hydraulic punch set with hole punches for carbon steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in pressure relief valve
Supply includes	Manual hydraulic punch, straight 7 split carbon steel punch with 3-fold pitch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5/19 mm HSS pilot drill Ø 10 mm Spacer bushing set (3-part) Plastic case
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø hole punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm 50.5 mm 63.5 mm

# Features

---

For thread	M16 M20 M25 M32 M40 M50 M63
Packaging unit	1 pc(s).
Net weight	5.3 kg
Gross weight	5.34 kg
Customs tariff number	82034000
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046
Product description	Hand hydraulic punch set straight M16,20,25,32,40,50,63 mm

---