

Rittal – The System.

Faster – better – everywhere.



AS 4055.080

Manual hydraulic punch set, M16 - M40

State: 2026-02-10 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.080 - Manual hydraulic punch set, M16 - M40

Manual hydraulic punch set with hole punches for carbon steel. Maximum machinable material thickness 2 or 3 mm.

Features

Model No.	AS 4055.080
Version	With cylinder head offset at 90° and rotatable through 360°
Product description	Manual hydraulic punch set with hole punches for carbon steel. Maximum machinable material thickness 2 or 3 mm.
Benefits	Extend tool life with a built-in pressure relief valve
Supply includes	Manual hydraulic punch 5 split carbon steel punch with 3-fold pitch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5/19 mm HSS pilot drill Ø 10 mm Spacer bushing set (3-part) Plastic case
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm
Ø hole punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For thread	M16 M20 M25 M32 M40

Features

Packaging unit	1 pc(s).
Net weight	4.1
Gross weight	4.16
Customs tariff number	84678900
EAN	4028177807952
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046