

Rittal – The System.

Faster – better – everywhere.



AS 4055.128

Round split plate punching machine

State: 2026-01-23 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.128 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.128
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp
Workable material	Stainless steel
Max. material thickness that can be machined for stainless steel	2.5 mm
Ø hole punch	28.3 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Net weight	0.157
Gross weight	0.181
Customs tariff number	82073010
EAN	4028177808034
ETIM 9	EC000156
ETIM 8	EC000156

Features

ECLASS 8.0

21049047