Rittal – The System.

Faster – better – everywhere.





AS 4055.163 Round split plate punching machine

State: 2025-11-18 (Source: rittal.com/ca-en)



AS 4055.163 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.163
Version	With 3-way split
Product description	
Supply includes	Die Stamp
Workable material	Stainless steel
Max. material thickness that can be machined for stainless steel	2.5 mm
Ø hole punch	63.5 mm
For thread	M63
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Net weight	1.025
Gross weight	1.098
Customs tariff number	82073010
EAN	4028177808164
ETIM 9	EC000156

© Rittal 2025

Features

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3