

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.163**

**Round split plate punching machine**

State: 2026-07-10 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.163 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.163  |
| Version  | With 3-way split   |
| Product description  |  |
| Supply includes  | Die<br>Stamp   |
| Workable material  | Stainless steel  |
| Max. material thickness that can be machined for stainless steel | 2.5 mm   |
| Ø hole punch   | 63.5 mm  |
| For thread   | M63  |
| Note   | Tension screws with a ball bearing must be used when operating with a wrench |
| Suitable for hydraulic bolt order number                         | 4055.663   |
| Tension screw (Ø x L)  | 19 x 75 mm   |
| Hydraulic tension screw Ø  | 19 mm  |
| Packaging unit   | 1 pc(s).   |
| Net weight   | 1.025 kg   |
| Gross weight   | 1.098 kg   |
| Customs tariff number  | 82073010   |
| ETIM 9   | EC000156   |
| ETIM 8   | EC000156   |

# Features

---

ECLASS 8.0

21049047

---

Product description

Splitter hole punch, round for stainless steel, round, with triple splitting