

# Rittal – The System.

Faster – better – everywhere.



## AS 4055.225

## Hole punch, round

State: 2026-01-10 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4055.225 - Hole punch, round for carbon steel

For punching round cut-outs

## Features

Model No.	AS 4055.225
Version	With 3 cutting tips
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp Tension screw without ball bearing
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm
Ø hole punch	25.4 mm
For thread	M25
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packaging unit	1 pc(s).
Net weight	0.142
Gross weight	0.163
Customs tariff number	82073010
EAN	4028177808249

# Features

---

ETIM 9 EC000156

---

ETIM 8 EC000156

---

ECLASS 8.0 21049047