

Rittal – The System.

Faster – better – everywhere.



AS 4055.232 Hole punch, round

State: 2026-05-05 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.232 - Hole punch, round for carbon steel

For punching round cut-outs

Features

Model No.	AS 4055.232
Version	With 3 cutting tips
Supply includes	Die Stamp Tension screw without ball bearing
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm
Ø hole punch	32.5 mm
For thread	M32
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packaging unit	1 pc(s).
Net weight	0.219 kg
Gross weight	0.242 kg
Customs tariff number	82073010
ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047

Features

Product description

Sheet metal punch round Ø 32,5 mm