

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.528**

**Round split plate punching machine**

State: 2025-07-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.528 - Round split plate punching machine For sheet steel, with 3-way pitch

For punching round cut-outs

## Features

Model No.	AS 4055.528
Version	With 3-way split
Product description	
Supply includes	Die Stamp
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm
Ø hole punch	28.3 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packaging unit	1 pc(s).
Net weight	0.143
Gross weight	0.167
Customs tariff number	82073010
EAN	4028177808690
ETIM 9	EC000156

# Features

ETIM 8	EC000156
ECLASS 8.0	21049047