

Rittal – The System.

Faster – better – everywhere.



AS 4055.263

Hole punch, round

State: 2025-09-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.263 - Hole punch, round for carbon steel

For punching round cut-outs

Features

Model No.	AS 4055.263
Version	With 3 cutting tips
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp Tension screw without ball bearing
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	3 mm
Ø hole punch	63.5 mm
For thread	M63
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Net weight	1.175
Gross weight	1.249
Customs tariff number	82073010
EAN	4028177808386
ETIM 9	EC000156

Features

ETIM 8	EC000156
ECLASS 8.0	21049047