

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.537**

**Round split plate punching machine**

State: 2026-05-08 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.537 - Round split plate punching machine For sheet steel, with 3-way pitch

For punching round cut-outs

## Features

|  |  |
|--|--|
| Model No.  | AS 4055.537  |
| Version  | With 3-way split   |
| Product description  |  |
| Supply includes  | Die<br>Stamp   |
| Workable material  | Carbon steel   |
| Max. material thickness that can be machined for sheet steel | 3 mm   |
| Ø hole punch   | 37 mm  |
| Note   | Tension screws with a ball bearing must be used when operating with a wrench<br>Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number                     | 4055.663   |
| Tension screw (Ø x L)  | 19 x 55 mm   |
| Hydraulic tension screw Ø                                    | 19 mm  |
| Packaging unit   | 1 pc(s).   |
| Net weight   | 0.281 kg   |
| Gross weight   | 0.314 kg   |
| Customs tariff number  | 82073010   |
| ETIM 9   | EC000156   |
| ETIM 8   | EC000156   |

# Features

---

ECLASS 8.0

21049047

---

Product description

Splitter hole punch, round for sheet steel, with triple splitting