


**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.561**

**Round split plate punching machine**

State: 2024-05-22 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.561 - Round split plate punching machine For sheet steel, with 3-way pitch

For punching round cut-outs

## Features

Model No.	AS 4055.561
Version	With 3-way split
Product description	
Supply includes	Die Stamp
Max. material thickness that can be machined for sheet steel	3 mm
Ø hole punch	61.5 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Weight/packaging unit	0.841 kg
Customs tariff number	82073010
EAN	4028177808812
ETIM 7.0	EC000156
ECLASS 8.0	21049047