

Rittal – The System.

Faster – better – everywhere.



AS 4055.580

**Split plate punching machine set
M16 to M40**

State: 2026-03-12 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.580 - Split plate punching machine set M16 to M40 For sheet steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.580
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 dies 5 stamps Plastic case
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm 2 mm 2 mm 3 mm 3 mm
Ø hole punch	16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm
For thread	M16 M20 M25 M32 M40
Note	Tension screws with a ball bearing must be used when operating with a wrench

Features

Suitable for hydraulic bolt order number	4055.661 4055.661 4055.661 4055.663 4055.663
Packaging unit	1 pc(s).
Net weight	1 kg
Gross weight	1.039 kg
Customs tariff number	82034000
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21044719
Product description	Splitter hole punch set, M16 to M40 for sheet steel, with triple splitting