Rittal - The System.

Faster – better – everywhere.





AS 4055.700

Busbar bending and hole punching unit CW 120-S


State: 2025-11-15 (Source: rittal.com/ca-en)



AS 4055.700 - Busbar bending and hole punching unit CW 120-S

The bending and hole punching unit from the CW 120-S product range is suitable for bending and punching busbars. Round holes and slots can be punched. The integrated precision laser makes the cutting and bending process easier. The bending and hole-punching unit can simply be placed on a workbench.





Features

Model No.	AS 4055.700
Version	Electrical protractor Length stop Mandrel R10 Bending die
Product description	The bending and hole punching unit from the CW 120-S product range is suitable for bending and punching busbars. Round holes and slots can be punched. The bending and hole-punching unit can simply be placed on a workbench.
Benefits	High level of bending and punching accuracy Simple tool change
Material thickness:	12 mm
Stamping/material width (max.)	120 mm
Bending/Leg length (min.)	50 mm
U-Bend (min.)	100 mm
Z-Bend (min.)	72 mm
Bending angle (max.)	90 °

© Rittal 2025 2

Features

Note	Leg length at a Z-bend depends on the material thickness
Bending (max.)	120 x 12 mm
Stamping (max.)	6.6 x 21.5 mm
Machine dimensions	Width: 700 mm
	Height: 410 mm
	Depth: 461 mm
Support area	Width: 756 mm
	Height: 426 mm
	Depth: 461 mm
Packaging unit	1 pc(s).
Net weight	64.5
Gross weight	67.5
Customs tariff number	84624900
EAN	4028177920668
ETIM 9	EC004303
ETIM 8	EC004303
ECLASS 8.0	36600804

Approvals

|--|

© Rittal 2025 3