### Rittal - The System.

Faster – better – everywhere.





AS 4055.581

# Split plate punching machine set M12 to M40

State: 2025-11-17 (Source: rittal.com/ca-en)



## AS 4055.581 - Split plate punching machine set M12 to M40 For sheet steel, with 3-way pitch

For punching round cut-outs

#### **Features**

Model No.	AS 4055.581
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	6 dies
	6 stamps
	Tension screw with ball bearing, Ø 6 x 40 mm
	Tension screw with ball bearing, Ø 9.5 x 50 mm
	Tension screw with ball bearing, Ø 19 x 55 mm
	HSS pilot drill Ø 10 mm
	1 can of lubricating paste
	Plastic case
Workable material	Carbon steel
Max. material thickness that can	1.5 mm
be machined for sheet steel	2 mm
	2 mm
	2 mm
	3 mm
	3 mm
Ø hole punch	
Ø hole punch	12.5 mm
Ø hole punch	12.5 mm 16.2 mm
Ø hole punch	
Ø hole punch	16.2 mm
Ø hole punch	16.2 mm 20.4 mm

© Rittal 2025

### **Features**

For thread	M12
	M16
	M20
	M25
	M32
	M40
Note	Tension screws with a ball bearing must be used when operating
	with a wrench
Suitable for hydraulic bolt order	4055.660
number	4055.661
	4055.661
	4055.661
	4055.663
	4055.663
Packaging unit	1 pc(s).
Net weight	2.2
Gross weight	2.256
Customs tariff number	82073010
EAN	4028177808843
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21044719

© Rittal 2025 3