


Rittal – The System.

Faster – better – everywhere.



AS 4055.582

Split plate punching machine set PG 9 to PG 21

State: 2025-08-26 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.582 - Split plate punching machine set PG 9 to PG 21 For sheet steel, with 3-way pitch

For punching round cut-outs

Features

Model No.	AS 4055.582
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	6 dies 6 stamps 2 tension screws with ball bearing, Ø 9.5 x 50 mm HSS pilot drill Ø 10 mm 1 tube of lubricating paste Plastic case
Workable material	Carbon steel
Max. material thickness that can be machined for sheet steel	2 mm
Ø hole punch	15.2 mm 18.6 mm 20.4 mm 22.5 mm 28.3 mm 30.5 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.661
Packaging unit	1 pc(s).
Net weight	1.08
Gross weight	1.09

Features

Customs tariff number	82073010
EAN	4028177808850
ECLASS 8.0	21044719