

Rittal – The System.

Faster – better – everywhere.



AS 4055.720 Electro-hydraulic pump

State: 2025-08-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.720 - Electro-hydraulic pump

The electro-hydraulic pump is used to drive the products from the CW 120-S product range.

Features

Model No.	AS 4055.720
Product description	The electro-hydraulic pump is used to drive the products from the CW 120-S product range.
Rated power	1.3 kW
Filling volume	3.2 l
Working volume	2.2 l
Flow rate (max.)	1.1 l/min
Oil (type)	HLP 46
Rated operating voltage	230 V, 50 Hz
Rated current	5.65 A
Machine dimensions	Width: 400 mm Height: 325 mm Depth: 335 mm
Support area	Width: 402 mm Height: 342 mm Depth: 397 mm
Permissible operating pressure (p. max.)	700 bar
Packaging unit	1 pc(s).
Net weight	32
Gross weight	34.5
Customs tariff number	84138100
EAN	4028177920644
ETIM 9	EC011047

Features

ETIM 8	EC011047
ECLASS 8.0	27301290

Approvals

Explanations	Declaration of conformity
--------------	---------------------------