
## Rittal – The System.

Faster – better – everywhere.





# SZ 4540.500 Combination angle

State: 2025-11-12 (Source: rittal.com/ca-en)



# SZ 4540.500 - Combination angle for VX, TS

For optimum distribution of tensile forces during transportation of bayed enclosures by crane.





#### **Features**

| Model No.                            | SZ 4540.500  |
|--------------------------------------|--|
| Product description                  | For optimum distribution of tensile forces during transportation of bayed enclosures by crane.                       |
| Material                             | Stainless steel 1.4301 (AISI 304)  |
| Supply includes                      | Assembly components  |
| Suitable for                         | Enclosure type: VX<br>TS   |
| Type rating according to UL 50E      | Type 1<br>Type 12  |
| Protection category NEMA             | NEMA 1, 12   |
| Protection category IP to IEC 60 529 | IP 55  |
| Packaging unit                       | 2 pc(s).   |
| Net weight                           | 1.2  |
| Gross weight                         | 1.4  |
| PCF/VE (cradle-to-gate)              | 5.3 kg CO2 eq (Cat B)  |
| Information regarding the PCF class  | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number                | 73182900   |
|                                      |  |

© Rittal 2025

### Features

| EAN        | 4028177976634 |
|------------|---------------|
| ETIM 9     | EC002622      |
| ETIM 8     | EC002622      |
| ECLASS 8.0 | 27189234      |

# **Approvals**

Approvals UL + C-UL - FTTA

© Rittal 2025 3