


Rittal – The System.

Faster – better – everywhere.



SZ 4140.020 Compact light

State: 2025-12-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4140.020 - Compact light

Compact light – slimline, space-saving light for use inside the enclosure



Features

| | |
|----------------------------|---|
| Model No. | SZ 4140.020 |
| Benefits | <p>Slimmer: Height and depth reduced by around 50%, takes up 75% less volume than conventional lights</p> <p>Faster: Universal quick-release fastening at TS punchings using clips, screws or powerful magnets (optional). Easy to insert at the sides or rear, fit light and you're done!</p> <p>Door-operated switch connection can be made using 2-pole connector</p> <p>Transparent light cover, fluted on inside</p> |
| Color | Similar to RAL 7035 |
| Supply includes | <p>Compact light with clip and screw mounting kits</p> <p>Light (bulb)</p> <p>Light cover</p> <p>Connection cable</p> <p>Assembly components</p> |
| Rated power | 14 W |
| Length of connection cable | 3 m |

Features

| | |
|---|--|
| Mounting distance screws | 725 mm |
| Ballast | Wide range voltage EB |
| Connection options | Integrated connection cable with open end Door-operated switch |
| Light (bulb) | T5 fluorescent lamp |
| Protection category | II (total insulation) |
| Switch (type) | Integrated, on/off/door-operated switch |
| Cable deflection via rear possible | Yes |
| Light cover | Yes |
| Light – installation type | Screw fastening Clip fastening Magnetic fastener (accessories) |
| Rated impulse withstand voltage, phase to earth | 1000 V AC |
| Rated impulse withstand voltage, phase to phase | 500 V AC |
| Rated insulation voltage | 500 V DC/1s |
| Mounting distance clip/magnet | 650 mm |
| Installation options | TS horizontal profile from roof frames: direct TS, SE vertical profile, direct SE profiles to the front and rear of roof frames: direct SE profiles to the side of roof frames: direct AE, CM, TP: with magnet mounting kit AE: with rail for interior installation |
| Note | Door-operated switch connection can be made using 2-pole connector |
| Note on Model No.: | Cable deflector across rear possible |
| Dimensions | Width: 705 mm Height: 59 mm Depth: 24 mm |
| Operating temperature range | -15 °C...45 °C |

Features

| | |
|-------------------------------------|--------------------------------|
| OUT_RATED_CURRENT_110_60 | 0.149 - 0.216 A |
| Rated current | 0.073 - 0.127 A |
| Storage temperature range | -20 °C...70 °C |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Protection category IP to IEC 60529 | IP 20 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.6 |
| Gross weight | 0.62 |
| Customs tariff number | 94054990 |
| EAN | 4028177522749 |
| E-Number Sweden | E4302501 |
| ECLASS 8.0 | 27189241 |