

Rittal – The System.

Faster – better – everywhere.



TS 4696.000 Support Strip

State: 2025-08-30 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4696.000 - Support Strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Model No.	TS 4696.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm hole pattern
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	540 mm
Installation options VX	In enclosure width/depth 600 mm
Installation options VX SE	In enclosure width/depth 600 mm, on the outer mounting level
Installation options AX	In door width 600 mm, with cam lock In door width 600 mm, with 3-point lock system, in the hinged door
Installation options AX stainless steel	In door width 600 mm, in the single-action door, in conjunction with the punched door strip
Installation options PC	In enclosure width 600 mm, on the outer mounting level
Installation options IW	In enclosure width/depth 600 mm, on the outer mounting level
Installation options TS	In enclosure width/depth 600 mm, on the outer mounting level

Features

Installation options AE	In enclosure width/height 600 mm, in conjunction with rail for interior installation AE
Installation options TP	In consoles for 3-part assembly, at the height of the enclosure cover, in conjunction with rail for interior installation for TP, compact enclosure HD
Installation options VX Base	In base/plinth width/depth 600 mm on the base/plinth panels, in conjunction with base/plinth installation bracket
Suitable for	Enclosure type: VX TS VX SE TP PC IW AX AE Suitable for width/depth: 600 mm
Suitable for	VX base system
Packaging unit	20 pc(s).
Net weight	5.22
Gross weight	5.54
PCF/VE (cradle-to-gate)	21.2 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177108158
E-Number Sweden	E3465252
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261