

# Rittal – The System.

Faster – better – everywhere.



## PC 4650.150

## PC enclosure system

State: 2025-12-16 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PC 4650.150 - PC enclosure system Stainless steel

PC enclosure systems based on VX SE made of stainless steel 1.4301, (AISI 304). Identical design principle to carbon steel PC. Convenient rear door allows easy access for service work. High access protection due to molded side panels and roof as well as internal visible door locking and lockable keyboard drawer.



## Features

Model No.	PC 4650.150
Version	Stainless steel with glazed door at the top, keyboard drawer and component shelf
Material	Housing: Stainless steel 1.4301 (AISI 304), 1.5 mm Rear door: Stainless steel 1.4301 (AISI 304), 2.0 mm Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm Monitor field: Single-pane safety glass, 4 mm
Surface finish	Brushed, grain 400
Supply includes	Housing, solid top and sides Rear door with locking rod Glazed door at the top, latched from the inside Component shelf Keyboard drawer with fold-down front door for handrest and mousepad tray Lock insert, lock no. 3524 E Bottom door with locking rod Base plates, divided

# Features

Dimensions	Width: 600 mm Height: 1,600 mm Depth: 630 mm
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Base material	Stainless steel 1.4301 (AISI 304)
Packaging unit	1 pc(s).
Net weight	98.5
Gross weight	100.8
EAN	4028177959491
ETIM 9	EC002502
ETIM 8	EC002502
ECLASS 8.0	27180501

# Approvals

Certificates	Surface finish
Explanations	Declaration of conformity