

Rittal – The System.

Faster – better – everywhere.



TS 4694.000 Support Strip

State: 2026-04-05 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4694.000 - Support Strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Model No.	TS 4694.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm hole pattern
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	340 mm
Installation options VX	In enclosure width/depth 400 mm, on the outer mounting level
Installation options VX SE	In enclosure width/depth 400 mm, on the outer mounting level
Installation options AX	In door width 400 mm, with cam lock
Installation options TS	In enclosure width/depth 400 mm, on the outer mounting level
Installation options TP	In TP pedestal and one-piece console pedestal, in enclosure depth 400 mm, in conjunction with rail for interior installation for TP, compact enclosure HD
Installation options VX Base	In base/plinth width/depth 400 mm on the base/plinth panels, in conjunction with base/plinth installation bracket

Features

Suitable for	Enclosure type: VX TS VX SE TP AX Width/depth: 400 mm
Suitable for	VX base system
Packaging unit	20 pc(s).
Net weight	3.2 kg
Gross weight	3.52 kg
PCF/VE (cradle-to-gate)	13.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	TS support strip, for VX, TS, VX SE, TP, for outer mounting level: for W/D: 400 mm, L: 340 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------