

# Rittal – The System.

Faster – better – everywhere.



## VX 5308.113

## VX IT network/server enclosure

State: 2026-06-21 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5308.113 - VX IT network/server enclosure with ventilated doors, with 19" standard profile rails

VX IT network/server enclosure, ventilated, for room climate control. 19" interior installation with depth-variable 19" profile rails in the standard version, available in a range of size variants.



## Features

Model No.	VX 5308.113
Version	Vented Standard with 19" mounting rails
Material	Carbon steel Aluminum Front door: aluminum, 1.25 mm Back door: carbon steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Interior: Spray-finished Rear door and roof: dipcoat-primed, powder-coated Front door: Aluminum, anodized/spray-finished
General color	RAL 7035
Color	Enclosure frame, rear door and roof: RAL 7035 Front door: Vertical sections, silver colored and horizontal sections, RAL 9005 Interior installation, vent grille at the front: RAL 9005 Handle and hinges: RAL 9005

# Features

Supply includes	<p>VX cabinet frame with doors and roof plate</p> <p>Aluminum carbon steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges</p> <p>Carbon steel door at the rear, vented (free area in perforated carbon steel part approx. 85 %)</p> <p>Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E</p> <p>Profile rails, 482.6 mm (19")</p> <p>Spacers, height 50 mm, for raising the cover plate above the fan breakout in the roof panel, for passive ventilation (enclosed) Not required for variants without cutout.</p> <p>12 x 19" fasteners 1 U, contacting (supplied)</p> <p>25 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, with cable entry in the corner areas front and rear</p> <p>Carbon steel door, rear, vertically divided, 180° hinges</p>
Dimensions	<p>Width: 600 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,000 mm</p>
Height units	42 U
Mounting space to 19" level, front/rear	87 mm / 720 mm
Installation position in 19" area	front and rear
Distance between levels as delivered	720 mm
19" attachment	with mounting bracket screw-fastened to the frame at the top and bottom
Version	Standard
Roof version	multi-piece, with cable entry in the corner areas front and rear
Design of rear door	Carbon steel door, vertically divided, 180° hinges
Design for front door	Aluminum carbon steel door, vented, one-piece, 180° hinges
Versions of profile rails	19" standard profile rails in VX IT
Floor version	open

# Features

Design of 19" mounting level(s)	front and rear
Design of position of profile rails	19" level, front and rear
Load capacity	15,000 N
Max. load capacity (static) per cabinet according to UL 2416	12,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	70.83 kg
Gross weight	81.2 kg
Customs tariff number	94032080
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207
Product description	VX IT, 19" mounting angles, standard, front and rear, vented, WHD: 600 x 2000 x 1000 mm, 42 U

# Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration Declaration of conformity Declaration of conformity UK