

Rittal – The System.

Faster – better – everywhere.



CM 5115.500

CM Compact System Enclosures

State: 2026-04-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CM 5115.500 - CM Compact System Enclosures

Housing with door made from sheet steel with mounting plate and open base to accommodate base plates. Protection category IP 55. A symbiosis of the enclosure benefits of Rittal compact enclosures, and the configuration diversity of the TS 8 baying enclosure system. Perforated mounting strips in the door for fast attachment of support strips, cable conduit holders and covers.



Features

Model No.	CM 5115.500
Material	Housing: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with hinged door(s) 3-point locking system with double-bit insert Mounting panel Open base for individual cable entry
Protection category NEMA	NEMA 12 with selection of the appropriate base plate or trim panel
Protection category IP to EN 60529	IP 55 with selection of the appropriate base plate or trim panel
IK code	IK08

Features

Dimensions	Width: 800 mm Height: 1,000 mm Depth: 400 mm
Dimensions of mounting plate (W x H)	740 mm x 955 mm
Number of doors	1
Interchangeable door catch	Yes
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	58.5 kg
Gross weight	59.5 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	CM Compact system enclosure, WHD: 800x1000x400 mm, Sheet steel, with mounting plate, single-door, open base

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK