

# Rittal – The System.

Faster – better – everywhere.



## DK 5302.014 Air Baffle Plate

State: 2026-06-05 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.014 - Air Baffle Plate for VX IT 19" standard profile rail

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

Model No.	DK 5302.014
Benefits	For targeted increase of energy efficiency of air conditioning Vertical brush strip for collision-free shielding with installed bar systems on the outer mounting level.
Applications	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material	Carbon steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Color	RAL 9005
Supply includes	2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly components 6 blind panels, 482.6 mm (19"), 1 U

# Features

Mounting tip	<p>For partitioning, the vertical trim panels with brush strips can be mounted to both the front and rear 19" profile rails.</p> <p>The horizontal trim panels with brush strips can only be mounted on the front 19" profile rails.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p>
Suitable for	Width: = 800 mm Height: = 2,000 mm
Packaging unit	1 pc(s).
Net weight	8.26 kg
Gross weight	8.48 kg
PCF/VE (cradle-to-gate)	33.1 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	56090000
ETIM 9	EC000331
ECLASS 8.0	27189272
Product description	Air baffle plate, for VX IT 19" mounting angles, standard, to separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. WxH: 800x2000 mm, RAL 9005