

Rittal – The System.

Faster – better – everywhere.



DK 5302.035 Slide Rails, 1U, Depth-Variable

State: 2026-05-12 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.035 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .



Features

| | |
|----------------------|--|
| Model No. | DK 5302.035 |
| Benefits | Tool-free, time-saving one-person assembly from the front of the enclosure All three mounting holes in the EIA system punchings are available for screw-fastening the equipment Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible |
| Applications | For assembly on the front mounting level To support heavy installed equipment. To adapt to individual distances between 19" levels |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options | 482.6 mm (19") L-profile rails, front and rear 482.6 mm (19") mounting frames, front and rear for 19" standard profile rails for VX IT 19" dynamic profile rails |
| Load capacity | 1500 N |
| Note | Effective contact surface 25 mm per side |

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX IT TE TX CableNet |
| Distance between levels | 600 - 825 mm |
| Packaging unit | 2 pc(s). |
| Net weight | 2.86 kg |
| Gross weight | 3.06 kg |
| PCF/VE (cradle-to-gate) | 11.7 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | Slide rail, 1 U, variable depth, for VX IT profile rails standard and dynamic, for TS IT L-profile rails, for TE mounting frame; For mounting on the front mounting level; Load capacity 1500 N. |