

Rittal – The System.

Faster – better – everywhere.



DK 5501.400

Slide rail, 2U, fixed installation

State: 2025-12-07 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.400 - Slide rail, 2U, fixed installation for VX IT

Mounted on 19" mounting level.

Features

Model No.	DK 5501.400
Product description	System punchings to mount accessories and ventilate active components.
Applications	For mounting on a 19" mounting level
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	150 mm
Installation options	for 19" standard profile rails for VX IT 19" dynamic profile rails
Load capacity	300 N, static
Packaging unit	2 pc(s).
Net weight	0.62
Gross weight	0.703
PCF/VE (cradle-to-gate)	2.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177678958
E-Number Sweden	E7239598
ETIM 9	EC002620
ECLASS 8.0	27189261