

Rittal – The System.

Faster – better – everywhere.



DK 5501.615

Component Shelf 2 U, Static Installation

State: 2025-07-25 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.615 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.



Features

| | |
|-------------------------------------|--|
| Model No. | DK 5501.615 |
| Version | 19" |
| Product description | Mounted on vertical 482.6 mm (19") rails. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 9005 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm Depth: 250 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 2.078 |
| Gross weight | 2.125 |
| PCF/VE (cradle-to-gate) | 9.5 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 73269098 |
| EAN | 4028177679054 |
| E-Number Sweden | E7239584 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |