

Rittal – The System.

Faster – better – everywhere.



DK 5501.430

Slide rail, 1U, fixed installation

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

DK 5501.430 - Slide rail, 1U, fixed installation for VX IT, TS IT, TX CableNet

Mounted between front and rear mounting levels.

Features

Model No.	DK 5501.430
Product description	Side system punchings to mount accessories and ventilate active components that exhaust air from the side.
Benefits	Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels
Applications	For assembly on the front mounting level To support heavy installed equipment.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Distance between mounting levels	545 mm
Length	475 mm
Installation options	for 19" standard profile rails
Mounting tip	The 19" space between levels in the VX IT must be adjusted accordingly prior to installation
Load capacity	800 N, static
Note	Effective contact surface 35 mm per side
Contact surface	Width: 35 mm
Suitable for	Enclosure type: VX IT TS IT
Packaging unit	2 pc(s).
Net weight	1.2

Features

Gross weight	1.4
PCF/VE (cradle-to-gate)	4.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73269098
EAN	4028177678989
E-Number Sweden	E7239601
ETIM 9	EC002620
ECLASS 8.0	27189261