


Rittal – The System.

Faster – better – everywhere.



DK 5501.460

Slide Rails, 1U, Depth-Variable

State: 2026-02-09 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 5501.460 - Slide Rails, 1U, Depth-Variable for VX IT, TE, TX CableNet

For mounting between a front and a rear mounting level .



Features

| | |
|----------------------|---|
| Model No. | DK 5501.460 |
| Benefits | <p>Tool-free, time-saving one-person assembly from the front of the enclosure</p> <p>All three mounting holes in the EIA system punchings are available for screw-fastening the equipment</p> <p>Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible</p> |
| Applications | <p>For assembly on the front mounting level</p> <p>To support heavy installed equipment.</p> <p>To adapt to individual distances between 19" levels</p> |
| Material | Carbon steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly components |
| Installation options | <p>482.6 mm (19") L-profile rails, front and rear</p> <p>482.6 mm (19") mounting frames, front and rear</p> <p>for 19" standard profile rails</p> |
| Load capacity | 800 N |
| Note | Effective contact surface 25 mm per side |

Features

| | |
|-------------------------------------|--|
| Suitable for | Enclosure type: VX IT TE TX CableNet |
| Distance between levels | 400 - 600 mm |
| Packaging unit | 2 pc(s). |
| Net weight | 2.164 |
| Gross weight | 2.34 |
| PCF/VE (cradle-to-gate) | 9 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177679016 |
| E-Number Sweden | E7239696 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |