


Rittal – The System.

Faster – better – everywhere.



DK 5501.615

Component Shelf 2 U, Static Installation

State: 2025-08-14 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.615 - Component Shelf 2 U, Static Installation

Component shelves 2 U, fixed, for attachment to 19" system punchings. Load capacity: 25 kg.



Features

Model No.	DK 5501.615
Version	19"
Product description	Mounted on vertical 482.6 mm (19") rails.
Material	Carbon steel
Surface finish	Spray-finished
Color	RAL 9005
Load capacity	25 kg surface load, static
Note	Not suitable for combination with telescopic slides.
Dimensions	Width: 482.6 mm Depth: 250 mm
Packaging unit	1 pc(s).
Net weight	2.078
Gross weight	2.125
PCF/VE (cradle-to-gate)	9.5 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared

Features

Customs tariff number	73269098
EAN	4028177679054
E-Number Sweden	E7239584
ETIM 9	EC002620
ECLASS 8.0	27189261