


# Rittal – The System.

Faster – better – everywhere.



## DK 5506.220

## TS IT Network/Server Enclosure

State: 2025-07-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5506.220 - TS IT Network/Server Enclosure with glazed door for rack climate control, North American version

TS IT with glazed door for conventional networking tasks and for use with direct, rack-related climate control. This North American version is RAL 9005.

## Features

Model No.	DK 5506.220
Material	Carbon steel Aluminum Viewing door: Single-pane safety glass, 3 mm
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005
Supply includes	Enclosure frame TS 8 with doors and roof plate 12 x 19" fasteners 1 U, contacting (supplied) 50 multi-tooth screws, conductive (supplied loose) Glazed aluminum door, front, 180° hinges Carob steel door rear, closed, vertically divided, 180° hinges Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E Roof plate, multi-piece, removable, for horizontal cable entry at the rear and covered cut-out for fan mounting plate Spacers to raise the fan cover plate, for passive cooling (supplied loose)
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 600 mm
Height units	42 U

# Features

Height units	42 U
Distance between levels as delivered	545 mm
Design doors	Solid
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Load capacity	15,000 N
Note	The door-opening angle may vary depending on site requirements or applications
Base material	Carbon steel
Packaging unit	1 pc(s).
EAN	4028177678620
ETIM 9	EC002499
ECLASS 8.0	27180207

# Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------