

**Rittal – The System.**

Faster – better – everywhere.



**DK 5511.151**

**TS IT Network/Server Enclosure**

State: 2026-06-21 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# DK 5511.151 - TS IT Network/Server Enclosure with glazed door, pre-configured, with 19" mounting frame

TS IT, sealed, for direct enclosure-specific climate control. Supplied pre-assembled with a selection of practical equipment. 482.6 mm (19") interior installation with 482.6 mm (19") mounting frame for a load capacity of up to 1,500 kg, available in a range of size variants.

## Features

|                |  |
|----------------|--|
| Model No.      | DK 5511.151  |
| Material       | Carbon steel<br>Aluminum<br>Base/plinth corner piece: Carbon steel<br>Base/plinth trim panels, front/rear: Carbon steel<br>Corner and baying covers: Plastic<br>Viewing door: Single-pane safety glass, 3 mm |
| Surface finish | Enclosure frame: Dipcoat-primed<br>Interior installation: Dipcoat-primed<br>Doors, roof and side panels: Dipcoat-primed, powder coated   |
| General color  | RAL 7035   |
| Color          | Housing frame and panels: RAL 7035<br>Interior installation, base/plinth: RAL 9005   |

# Features

|   |   |
|---|---|
| Supply includes                         | <p>Enclosure frame TS 8 with doors, roof plate, base/plinth and side panels</p> <p>Glazed aluminum door, front, 180° hinges</p> <p>Lock front and rear: Comfort handle for semi-cylinders and security lock 3524 E</p> <p>Two 482.6 mm (19") mounting frames, front and rear, depth-variable Spacers, height 50 mm, for raising the cover plate above the fan breakout in the roof panel, for passive ventilation (enclosed) Not required for variants without cutout.</p> <p>Connection accessories for potential equalization with a central grounding point, pre-assembled</p> <p>12 x 19" fasteners 1 U, contacting (supplied)</p> <p>50 multi-tooth screws, conductive (supplied loose)</p> <p>Base Mount</p> <p>Base module mounted at front as infill panel</p> <p>Base/plinth system VX, 100 mm, vented</p> <p>Base/plinth corner pieces and trim panels, side, screw-fastened</p> <p>Base/plinth trim panels for front and rear as well as baying cover included</p> <p>Side panels, one-piece, lockable</p> <p>4 M12 leveling feet incl. base/plinth adapter (supplied loose)</p> <p>4 cable clamp rails (T-head) for outer mounting level, to fit enclosure depth (supplied loose)</p> <p>10 cable shunting rings, metal, 125 x 65 mm (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate</p> <p>Carob steel door rear, closed, vertically divided, 180° hinges</p> |
| Dimensions                              | <p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,200 mm</p>   |
| Height units                            | 42 U  |
| Height units                            | 42 U  |
| Height incl. base/plinth                | 2,100 mm  |
| Mounting space to 19" level, front/rear | 147 mm / 305 mm   |
| Distance between levels as delivered    | 745 mm  |

# Features

|                                 |   |
|---------------------------------|---|
| Design of 19" mounting level(s) | Mounting frame, 482.6 mm (19")  |
| Load capacity                   | 15,000 N  |
| Note                            | The door-opening angle may vary depending on site requirements or applications          |
| Base material                   | Carbon steel  |
| Packaging unit                  | 1 pc(s).  |
| Net weight                      | 172 kg  |
| Gross weight                    | 187 kg  |
| Customs tariff number           | 94032080  |
| ETIM 9                          | EC002499  |
| ECLASS 8.0                      | 27180207  |
| Product description             | TS IT, 19" mounting frame, glazed door, WHD: 800 x 2000 x 1200 mm, 42 U, pre-configured |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Certificates | Surface finish            |
| Explanations | Declaration of conformity |