

# Rittal – The System.

Faster – better – everywhere.



## CP 6321.000

## Operating housing for desktop TFT up to 24"

State: 2025-06-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6321.000 - Operating housing for desktop TFT up to 24"

Integrated VESA 75/100 mount. Effective and attractive protection for commercially available desktop TFTs up to 24" in 16:9/16:10 formats. High protection category of IP 65.

## Features

Model No.	CP 6321.000
Version	Viewing window with single-pane safety glass
Product description	For the installation of standard, commercially available desktop TFTs with a screen diagonal of up to 24" in the formats 16:9/16:10
Material	Housing and door: Carbon steel Handle strips: Aluminum Cover caps: Plastic Viewing window: Single-pane safety glass TFT holder: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodized
Color	Housing and door: RAL 7035 Handle strip: Natural anodized Cover caps: Similar to RAL 7024
Supply includes	Housing with cut-out and reinforcement for support arm connection Ø 130 mm Viewing window Holder for desktop TFT with VESA 75/100 locator Side handle strips and cover caps Rear door with r/h hinge Cam lock with 3 mm double-bit insert
Dimensions	Width: 650 mm Height: 450 mm Depth: 155 mm
Protection category IP to IEC 60529	IP 65

# Features

No. of locks	1
Note	<p>The support arm connection and door catch may be swapped over by rotating the enclosure</p> <p>Optional: Support arm connection Ø 130 mm, preformed off-center in the reinforcement plate, easily drilled out</p> <p>Lock insert may be exchanged for 27 mm lock inserts, type A, lock cylinder, plastic handles and T-handles, type B</p>
Base material	Aluminum
Lock	<p>Lock version: Cam</p> <p>No. of locks: 1</p> <p>Lock Insert: 3 mm double-bit</p>
Packaging unit	1 pc(s).
Net weight	16.468
Gross weight	17.335
Customs tariff number	94032080
EAN	4028177697324
ECLASS 8.0	27180505

# Approvals

Approvals	Bureau Veritas
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>