

Rittal – The System.

Faster – better – everywhere.



SE 5854.600

VX SE enclosure system

State: 2026-02-01 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

SE 5854.600 - VX SE enclosure system Stainless steel

Individual stainless steel enclosure with stable enclosure body, two integrated mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible with the VX25 baying system. Enclosure widths ranging from 600 to 1200 mm. Increases efficiency as side panels do not have to be mounted.



Features

| | |
|-----------------|---|
| Model No. | SE 5854.600 |
| Material | <p>Housing: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed</p> <p>Door: Stainless steel 1.4301 (AISI 304), 2.0 mm, exterior brushed</p> <p>Rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed</p> <p>Base plates: Stainless steel 1.4301 (AISI 304), 1.5 mm</p> <p>Mounting panel: Carbon steel, 3.0 mm</p> |
| Surface finish | <p>Housing, door and rear panel: Brushed, grain 400</p> <p>Base plates: Uncoated</p> <p>Mounting panel: Zinc-plated</p> |
| Supply includes | <p>Housing, solid top and sides</p> <p>Door(s)</p> <p>Right-hand door catch on single-door enclosures may be swapped to the left</p> <p>Rear panel, detachable</p> <p>Mounting panel</p> <p>Base Plates</p> <p>Lock: 3 mm double-bit</p> <p>2 punched rails, 18 x 39 mm</p> |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 1,000 mm Height: 1,800 mm Depth: 400 mm |
| Dimensions of mounting plate (W x H) | 899 mm x 1,696 mm |
| Protection category IP to EN 60 529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Type rating according to UL 50E | Type 1 Type 2 Type 3 Type 3R Type 12 |
| IK code | IK10 |
| Number of doors | 1 |
| Note | Due to the hardness of the material, we recommend using metal multi-tooth screws 2486.400 for the interior installation. |
| Base material | Stainless steel 1.4301 (AISI 304) |
| Packaging unit | 1 pc(s). |
| Net weight | 133 |
| Gross weight | 140.4 |
| EAN | 4028177959330 |
| E-Number Sweden | E3465423 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Certificates | Surface finish Protection category |
| Explanations | Declaration of conformity Declaration of conformity UK |
