

Rittal – The System.

Faster – better – everywhere.



CP 6380.020

Optipanel

State: 2026-02-05 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

CP 6380.020 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.



Features

Model No.	CP 6380.020
Version	Support arm connection, rectangular 120 x 65 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive heat dissipation. Low weight coupled with high stability Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section Corner pieces: Die-cast zinc Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized. Corner pieces: RAL 7035 Corner protectors: Similar to RAL 7024
Supply includes	Housing with hinged rear panel Seals
Dimensions	Width: 474 mm Height: 387 mm Depth: 110 mm

Features

Installation depth	100 mm
Protection category IP to IEC 60529	IP 65
Suitable for front panel width	430 mm
Suitable for front panel height	343 mm
Version	Service access from rear
Note	<p>The support arm connection may be swapped over by rotating the enclosure</p> <p>3 mm double-bit lock insert may be exchanged for 41 mm lock inserts, plastic handles and T handles, type C</p> <p>Rear panel hinges on the longest enclosure side</p>
Base material	Aluminum
Lock	<p>Lock version: Cam</p> <p>No. of locks: 2</p> <p>Lock Insert: 3 mm double-bit</p>
Packaging unit	1 pc(s).
Net weight	5.898
Gross weight	6.208
EAN	4028177429079
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	<p>Declaration of conformity</p> <p>Declaration of conformity UK</p>