Rittal – The System.

Faster - better - everywhere.





CP 6380.410 Optipanel

State: 2025-10-27 (Source: rittal.com/ca-en)



CP 6380.410 - Optipanel

Aluminum housing, high thermal conductivity for optimum passive heat dissipation. For smaller panels and control solutions. Extremely slim design, requires slightly more space than the installations themselves.







Features

Model No.	CP 6380.410
Version	Support arm connection Ø 130 mm
Benefits	Aluminum housing, high thermal conductivity for optimum passive
	heat dissipation.
	Low weight coupled with high stability
	Compatible with all Rittal stand and support arm systems
Material	Housing: Extruded aluminum section
	Corner pieces: Die-cast zinc
	Corner protectors: Plastic
General color	Natural anodized
Color	Housing: Natural anodized.
	Corner pieces: RAL 7035
	Corner protectors: Similar to RAL 7024
Supply includes	Housing with hinged rear panel
	Seals
	Seals and assembly components for front panels
Installation depth	150 mm

© Rittal 2025

Features

Protection category IP to IEC 60 529	IP 65
Suitable for front panel width	520 mm
Suitable for front panel height	400 mm
Version	Service access from rear
Note	The support arm connection may be swapped over by rotating the enclosure
	3 mm double-bit lock insert may be exchanged for 41 mm lock
	inserts, plastic handles and T handles, type C
	Rear panel hinges on the longest enclosure side
Base material	Aluminum
Lock	Lock version: Cam
	No. of locks: 2
	Lock Insert: 3 mm double-bit
Packaging unit	1 pc(s).
Net weight	9.795
Gross weight	10.311
EAN	4028177663169
ETIM 9	EC002504
ECLASS 8.0	27180505

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3