

Rittal – The System.

Faster – better – everywhere.



SM 6446.030 Built-in keyboard 19"/4 U

State: 2026-05-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 6446.030 - Built-in keyboard 19"/4 U with integral touchpad

The integral touchpad means there is no need to install a mouse in the correct protection category, and cabling is also reduced.



Features

Model No.	SM 6446.030
Product description	The integral touchpad means there is no need to install a mouse in the correct protection category, and cabling is also reduced. The short-stroke keys are easy to locate thanks to raised edges, are operated with a light touch and give good, tactile feedback.
Benefits	The separate number pad enables the parameters to be entered quickly Sealed, wipeable surface finish High level of mechanical and chemical resistance as per DIN 42 115.
Material	Front panel: Aluminum
Supply includes	USB connection cable, length 1.8 m Seal Drilling template Assembly components for surfaces
Dimensions	Width: 482.6 mm Height: 177 mm Depth: 30 mm
Number keys	2.6 N
Number keys	0.3 mm

Features

Interfaces	1 x USB
Number keys	105
Layout	German
Resolution capacitive touchpad	40 pixels/mm
Lifetime	3 million switching cycles
Dimensions	Thread: M5 Thread length: 20 mm
Operating temperature range	-40 °C...90 °C
Protection category IP to IEC 60529	IP 65 (at the front, sealed)
Packaging unit	1 pc(s).
Net weight	1.44 kg
Gross weight	1.82 kg
Customs tariff number	84716060
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	SM Built-in keyboard 19"/4 U, WHD: 482,6x177x30 mm, Installation depth: 23 mm, german, With integral touchpad

Approvals

Explanations	Declaration of conformity
--------------	---------------------------